Family of TOFD products

TIT

6

TOUGHBOOK

(•\$** @ @ b Ø

m 3.k m 1.2 x

WĴFi

CEN/TS 14751:2004 Compliant EN 5836:2000 Compliant



www.oko-ndt.com

PURPOSE	TOFD Systems are intended for mecha-	• flat objects;
	nized ultrasonic testing of welded joints using Time of Flight Diffraction (TOFD) tech- nique. The System is used for the butt welded joints UT at:	 tubes of medium and large diameters – OD not less than 12 in (300 mm) – de- pends on the scanner type; spherical and cylindrical oil and gas tanks – OD not less than 33 ft (10 m).
CONFIGURATIONS OF TESTED WELDED JOINTS:	 profile types: CRC-Evans, single J groove weld, single V groove weld, double V groove weld, x-welds, etc.; 	 wall thickness: .25 in (6 mm) to 12 in (300 mm); tube and plate material: standard carbon steels and some others.
PRODUCTS FAMILY OVERVIEW	 OKO Association presents several products which can be used according to the testing object and conditions specifics: TOFD MAN [™] is our latest solution for easy testing of both medium-diameter pipelines and large objects, primarily those that require the use of climbing equipment during the scanning process. All equipment of TOFD MAN [™] is put in a specially designed load-release jacket, thanks to which the weight of the equipment is practically not felt. TOFD 2.2 Lite scanner that is included into the standard-type system can be also attached to the jacket belt when testing is not beeng per- 	 formed. All data are transferred to a remote laptop or tablet via wireless Wi-Fi interface. To solve various NDT tasks, TOFD MAN[™] can be provided with one of our scanners: TOFD 2.11 PRO or TOFD 2.1 Dragonfly. TOFD 2.2 PRO System is based on a manual scanner TOFD 2.2 PRO that incorporates not only encoder and probes, but also electronics and battery. This scanner is ideal for testing large pipelines or other similar objects. Here, all data are transferred to a remote laptop or tablet via wireless Wi-Fi interface, too.
TOFD TECHNIQUE DESCRIPTION FEATURES AND COMPLIANCE WITH STANDARDS	Time of Flight Diffraction (TOFD) tech- nique is based on diffraction of ultrasonic waves from the tips of discontinuities. This method is even more reliable than traditional radiographic, pulse echo manual	UT and automated UT weld testing methods. TOFD offers great accuracy for measuring the critical through-wall size of crack-like-de- fects. The accuracy of better than ± 1 mm can be obtained in a wide range of material thickness
Testing scheme by TOFD technique	a c d b	 Main advantages of TOFD are: Detects defects regardless their orientation, in contrast to the pulse echo technique. In contrast to the radiography method, planar defects and cracks, which are not perpendicular to the measured surface can be detected. High degree of repeatability. Precise defect sizing capability. Fast scanning only along the weld. Full volume inspection in a single run. Immediate results and permanent digital records with graphic images.
Displaying the signals on A-scan		 Amplitude insensitive – acoustical cou- pling less critical
	1 - transmitter; 2 - receiver;	Setup independent of weld configuration.

TOFD Systems software consists of the queue of tabs guiding the inspector through step-by-step setup procedure, data acquisition and analysis. Software is both mouse and finger friendly so can be used on various types of computers - tablets, laptops, desktops, etc. Setup process is greatly facilitated due to wide usage of setup elements libraries - Geometry library, Materials library, Scanners library, Probes library, etc. So the major portion of the setup procedure shrinks to choosing of proper elements from those libraries. Complete setup packs suitable for particular testing tasks can be saved and then loaded at any time.

SOFTWARE	Armania Arm
THE SYSTEM SOFTWARE INCLUDES THE FOLLOWING PAGES (MODULES):	
The "Object" page ensures	: • selecting the test object geometry and set- • selecting the t

- ting up its geometrical dimensions;
 - selecting the type of test object material;
- type of a weld bevel and setting up all geometrical dimensions.





TOFD calibration

•

Fast and intuitive calibration procedure • can be done directly at the testing object . or in lab.

- The "TOFD calibration" page ensures:
- setting up the testing parameters for TOFD;
- carrying out the real-time TOFD cali- bration by saved data;
- generating the parameters matrix of calibration block reflectors; real-time check up of reflectors detec- •
 - saving the calibration results.

tion in calibration block;



Data acquisition

The "Data acquisition" page ensures:

- data display in a form of A-Scan together with TOFD-Scan during the testing • process;
- carrying out the testing and data acquisition with an auto stop of a testing mode •

by a distance predetermined by the operator;

- displaying the current scanner position (the coordinate along the scanning path) and the scanning speed;
- data synchronization during the testing

process by lateral wave;

- considering the scanning direction and capability to perform the confirming testing of regions with the loss of acoustic coupling;
- saving the testing results.



Data analysis

The "Data analysis" page ensures:

- review and analysis of saved data in a form of A-Scans and TOFD-Scans:
- quick and detailed analysis of testing results • while using two measuring gates (type: simple, hyperbolic, hyperbolic manual);
- discontinuities detected by TOFD shall be characterized by at least:
 - their position in the object (X and Y coordinates);
 - their length (ΔX);

- their depth and height ($Z, \Delta Z$);
- their type, limited to: "top-surface breaking", "bottom-surface breaking" or "inner".
- generating the defects table and its saving.

	Object	Scen	ner	TOFD	setup
1		Data	selectio		
	Even Time		Witness	e# 0	iperator.
21	06.06.2016 18	20.00			
12	08.05.2015 19	10.54			
22	08.06.2016 19	5145			
м	05.07.2016 13	5146	600	D	ooye hadri
15	05.07.0016.13	52.31	602	D	eeys Andri
1	05.07.2016 13	5412	603	D	işeyi kedeli
1	05.07.2016 13	0033	101	0	ieeys Andeli Ionei Andeli
	05.07.2016 14	02.10	100	0	and Andri
10	04.93.2016 16	4445			
61	04.10.2016 16	49.12			
	Data fibration po				
	Dute		- 14	en 193.1	18.2016 *
			, "	19.1	10.2006 7
	Welded joint #		-		
	Operator				
	Document param	41673			
	Cutting width			100	
		_			
	Print preview, Print			G	9 0
					-

- The "Reports" page ensures: generating the reports according to the requirements of Regulatory Documentation CEN/TS 14751:2004, ENV 583-6:2000;
 - · approval of report forms with the customer when necessary.

The software is designed for ease of use, flexibility and scalability, and is oriented for a touchscreen operation.

The user interface is optimized for the accelerated learning process and improving the efficiency of use.

TOFD PRO SYSTEM COMPOSITION

INDUSTRIAL LAPTOP OR TABLET WITH SOFTWARE



Shockproof industrial laptop/tablet with installed Microsoft Windows and special software for TOFD setup, data acquisition, analysis and reporting.

The System may contain of up to 4 data acquisition TOFD units. **DATA ACQUISITION** TOFD unit ensures data acquisition and transmission in real-time mode via Ethernet-inter-**TOFD UNIT** face to industrial notebook or tablet. Unit case is made of shock-proof material. 1 OR 2 AXIS ENCODER POWER SWITCH ON/OFF BUTTON GROUND



TOFD MAN ™ System

The system is designed for testing long be examined with the help of appropriate ment, also when performing an inspection welded joints of pipes, tanks, vessels, cis- probes. Depending on the inspection task, at height (climbing, rope access). Standard terns, ship hulls, bridges, etc. using TOFD TOFD MAN [™] system can be complete with technique. Circumferential welds with a di- another scanner (see "Scanners"). The hour battery to be put in the jacket. The ameter from 12 in (300 mm) can be in- amount of probe pairs can vary from 1 to spected on cylindrical objects. On 4. For good coupling, it is advised to use an It ensures handy probes setup. cylindrical, spherical, as well as complex- external coupling liquid supply system. In vature from 16 ft (5 m) to flatness, the scanner, But if absolute mobility is needed. system is capable of testing long welds in coupling media can be applied to the object any direction. Objects with wall thickness before testing, or a test object can be confrom .25 to 12 in (from 6 to 300 mm) can tinuously showered with water.



optimized for placement on the operator's connection to transmit data to PC. jacket, which does not impede the move-

delivery set of the system features an 8scanner is light-weighted and easy to guide.

In the course of and testing, all setup shaped objects with a radius of surface cur- this case, a water hose will come to the data are transfered to a remote PC (laptop or tablet) via Wi-Fi. A system for protecting the integrity of test data is provided, while they are fully stored inside the TOFD module and transferred to PC at the end of test-Configuration of the system is maximally ing. If required, it is possible to use a wire





The system is primarily intended for testing circumferential welds of large pipelines and other cylindrical objects with a diameter from 24 in (600 mm), as well as spherical objects with a diameter from 33 ft (10 m), wall thickness from .25 to 12 in (from 6 to 300 mm) inspected provided that the probes being changed.

'All-On-Board' philosophy of the system means that the scanner accommodates all electronics, including an 8-hour battery. The scanner is rigid, easy-to-guide and wireless due to the fact that TOFD module, power unit and Wi-Fi module are placed onboard. For good coupling, it is advised to use an external coupling liquid supply system. In

this case, a water hose will come to the scanner. But if absolute mobility is needed, coupling media can be applied to the object before testing, or a test object can be continuously showered with water. If required by the customer, it is possible to supply a modified standard-type scanner that would include not one but two pairs of probes.

A system for protecting the integrity of test data is provided, while they are fully stored inside the TOFD module and transferred to PC at the end of testing. If required, it is possible to use a wire connection to transmit data to PC.



TOFD SCANNERS

To meet requiremets of a variety of testing tasks soved wuth TOFD technique, OKO Association has developed and continue developing a product line of TOFD scanners presented below.

TOFD 2.2 Lite scanner

TOFD 2.2 Lite scanner is a great solution for testing of both butt welds at large objects (like oil and gas storages, ship hulls, etc) and circular butt welds on medium and large diameter pipelines – starting from dia 12 in (300 mm).

Scanner can carry one pair of probes and can be modified to carry 2 pairs of probes on request.

Scanner is light weighted and easy to guide. It ensures coupling liquid supply to the working surfaces of each probe individually for good coupling.









TOFD 2.11 PRO

TOFD 2.11 PRO scanner is intended for testing of the ring welded joints of pipes and boilers with the diameter above 24 in (600 mm) and wall thickness from .25 to 12 in (from 6 to 300 mm) and also flat and large diameter objects such as ships hulls, oil and gas storage tanks, etc.

This scanner can carry up to 2 pairs of probes and can be modified to carry up to 4 pairs of probes on request.

Scanner is rigid and comfortable to guide. It ensures coupling liquid supply to the working surfaces of each probe individually for good coupling.









TOFD 2.10 Dragonfly

TOFD 2.10 Dragonfly scanner has a wide range of applications: testing of welded joints of flat surfaces, longitudinal and ring welded joints of pipes with minimal outer diameter 24 in (600 mm) and thickness from .25 to 4 in (from 6 to 100 mm).



TOFD UNIT SPECIFICATIONS OF ALL SYSTEMS

- •
- Ultrasonic transducers connector _____2 (BNC) A/D converter _____10 bit (100 MHz) •
- Initial pulse _____ 50 400 V •
- •
- Gain _____110 dB Bandwidth _____0.2 27 MHz •
- Encoder _____ up to 2 axis encoder .

PRF	15 - 2000 Hz
Realtime averaging	1, 2, 4, 8, 16, 32, 64
Maximum scanning velocit	y100 mm/s
Operating	
temperature range	_from minus 20 °C to plus 50 °C
Protection level	IP65



Email: global-sales@oko-ndt.com www.oko-ndt.com